


For Vent Wiring or controller/thermostat connections, see literature packet or go to [www.bardhvac.com](http://www.bardhvac.com)

230/208-60-1  
240/220-50-1  
Per Nameplate



NOTE:  
THIS IS LOCATED  
IN UPPER CONTROL  
PANEL ON THE W42-72  
BROWN ON W24 MODELS  
BLUE ON W24 UNITS

Wire tucked in cable duct if no OD switch (only use with LAC)

Wire tucked in cable duct when no OD switch (only used with LAC)

Wire tucked in cable duct if no OD switch (only use with LAC)

NOTE: JUMPER PLUG MUST BE INSTALLED WHEN NO VENT OPTION IS INSTALLED

**WARNING**  
USE COPPER CONDUCTORS ONLY SUITABLE FOR AT LEAST 75° C.

**DANGER**  
ELECTRICAL SHOCK HAZARD DISCONNECT POWER BEFORE SERVICING.

**A**  
Wires Connect if Option Not Used

High Voltage	-----	-----	-----
Low Voltage	-----	-----	-----

99 Wire Identification numbers for Bard use only.

	Factory	Field	Optional
High Voltage			
Low Voltage			

4095-196 G