


For Vent Wiring or controller/thermostat connections, see literature packet or go to [www.bardhvac.com](http://www.bardhvac.com)

230/208-60-1  
240/220-50-1  
Per Nameplate



NOTE:  
THIS IS LOCATED  
IN UPPER CONTROL  
PANEL ON THE W42-72  
BROWN OR BLACK ON W24 MODELS  
BLUE OR WHITE ON W24 UNITS

Wire tucked in cable duct  
when no OD switch  
(only used with LAC)

Wire tucked in cable  
duct if no OD switch  
(only use with LAC)

NOTE: JUMPER PLUG  
MUST BE INSTALLED  
WHEN NO VENT OPTION  
IS INSTALLED

**WARNING**  
USE COPPER CONDUCTORS  
ONLY SUITABLE FOR AT LEAST  
75° C.

**DANGER**  
ELECTRICAL SHOCK HAZARD  
DISCONNECT POWER BEFORE  
SERVICING.

**A**  
Wires Connect  
if Option Not  
Used

High Voltage	-----	-----	-----
Low Voltage	-----	-----	-----

99 Wire Identification numbers  
for Bard use only.

	Factory	Field	Optional
High Voltage			
Low Voltage			

4095-196 H